

Email :
sales@schooleducationalinstruments.com
Phone: +91-0171-2601773

Product Name :
TIG Welding Machines

Product Code :
SCHOOL-WRK780030



Description :

TIG Welding Machines

Technical Specification :

Input voltage: 3 Phase 415+ 10%

Frequency: 50/60 Hz

No-load consumption: 60 W

Efficiency (%): 85

Power factor (COS ϕ): 0.93

Current of MMA (A): 0-300

Insulation class: H

Protection class: IP21, IP23

No-load voltage V: 80

Output current adjustment range (A): 0-300

Rated output voltage (V): 22

Rated duty cycle 35%: 300 A

Rated duty cycle 60%: 250 A

Rated duty cycle 100%: 210 A

Rated input power capacity: 10 KVA

Suitable welding thickness mm: 0.5 mm to 6mm

Welding Electrode: up to 6 mm

Weight (Approx.): 17 KG

Measurement (mm): 480 X 205 X 355

Quality Conformance: STQC, CE, ISO, EN

NAUGRA[®]

School Educational Instruments

Website: [www.https://www.schooleducationalinstruments.com/](https://www.schooleducationalinstruments.com/), **Email:** sales@schooleducationalinstruments.com

Address: Ambala Cantt, Haryana, India **Phone:** 91-0171-2643080